

COIL: 0 +25° C		CUSTOMER DATA SHEET	
RESISTANCE <u>160</u> NOMINAL VOLTAGE _ MUST OPERATE MUST RELEASE	12.0 VDC 6.4 VDC	\$ [BLUE BEAD
SHOCK <u>100</u> g's	5 TO <u>2000</u> CPS AT <u>20</u> g's <u>6 MS. Duration</u> <u>-65 °C TO</u> †125 °C	CONTACT RATING	Low level to
NOTES:		DR. 4-26-82	CK. OSW
		Communications Instruments, Inc.	
CUST. CII STANDARD	TYPE HFW RELAY	HFW4A	201GOO