


- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer LCP UL94-VO
Pin Brass Tin-plated

Circuit	Part No.	Dimensions mm		
		A	B	C
2	XD-XH-2ALT-XX	2.50	7.50	10.00
3	XD-XH-3ALT-XX	5.00	10.00	12.50
4	XD-XH-4ALT-XX	7.50	12.50	15.00
5	XD-XH-5ALT-XX	10.00	15.00	17.50
6	XD-XH-6ALT-XX	12.50	17.50	20.00
7	XD-XH-7ALT-XX	15.00	20.00	22.50
8	XD-XH-8ALT-XX	17.50	22.50	25.00
9	XD-XH-9ALT-XX	20.00	25.00	27.50
10	XD-XH-10ALT-XX	22.50	27.50	30.00
11	XD-XH-11ALT-XX	25.00	30.00	32.50
12	XD-XH-12ALT-XX	27.50	32.50	35.00
13	XD-XH-13ALT-XX	30.00	35.00	37.50
14	XD-XH-14ALT-XX	32.50	37.50	40.00
15	XD-XH-15ALT-XX	35.00	40.00	42.50
16	XD-XH-16ALT-XX	37.50	42.50	45.00

Ordering Information



GENERAL TOLERANCE			制图 DRAWING	01			深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd					
DIM TOL			审核 CHECK				产品名称 TITLE	XH (2.50) 单排 立贴		版本 REV.	A	
X.X ±0.30			批准 APPROVAL				产品料号 PART NO.	XD-XH-NALT-XX		单位 UNITS	mm	
X.XX ±0.20			比例 SCALE				材料 MATERIAL				页次 SHEET	1/1
X.XXX ±0.10			投影 Projection									
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°									