

**Operation:** SMT/卧式 2.5 $\phi$ 中型 三段音频连接器



**LTEM NO.:** PJ-208A (Series)

(L13.5 $\times$ W5.0 $\times$ H4.5 2.5 PHONE-JACK)

贴片卧式

侧向操作

精密部品

带导向柱

適合環保 **RoHS**




**Technical parameter**

PROJECT	LEVEL	A[better product]		B[average product]	
		Contact Rating			
Electrical	Initial Contact Resistance	50m $\Omega$ max.			
	Insulation Resistance	100M $\Omega$ min.500V DC	Skey/PD: 100M $\Omega$ min.300V DC		
Properties	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut		
	There No Load	6,000 Cycles	5,000 Cycles		
Durable Performance	Rated Load	5,000 Cycles	4,000 Cycles		
	Storage temp.	-35 $^{\circ}$ C~+75 $^{\circ}$ C(Operating Temp: )			
Operating Force		IF:5~15N MAX. (EF:10.0N MIN.)			
Heat Rrsistance		225 $^{\circ}$ C, 5sec. Manual:350 $^{\circ}$ C, 3sec.			

Material declaration		
No	NAME	Description
①	基座	PBT (Black)耐热塑胶
②	接觸端子#2	C5191R-H (t=0.20mm)磷铜[鍍基銀]
③	接觸端子#3	C5191R-H (t=0.20mm)磷铜[鍍基銀]
④	接觸端子#4	C5191R-H (t=0.20mm)磷铜[鍍基銀]
⑤	接觸端子#5	C5191R-H (t=0.20mm)磷铜[鍍基銀]

**CIRCUIT DIAGRAM**



Unit:mm

