

Product Features

1. Reliable seam sealed ceramic package
2. Wide operating temperature range
3. Superior performance and stringent reliability in harsh environment
4. AEC-Q200 Compliant
5. RoHS and REACH Compliant , Pb-free , Halogen-free
6. Industry Standard Package :
3.2 x 2.5 x 0.7 mm (AM Series)

Application :

- Automotive Wireless Communication
- In-Vehicle Infotainment system
- Camera , Radar , Lidar , TPMS , Smart Key
- Battery Management System , Body Control
- Power steering , Breaking System , Engine Control



Test condition

Ambient temperature : 25 ± 5°C


Relative humidity : 40% ~ 70%

● **Table 1 . Electrical Specifications**

Parameters	Symbol	Min.	Typ.	Max.	Units	Notes
Nominal Frequency	F	8 ~ 62.4			MHz	
Frequency Tolerance	FT	± 10			ppm	@25°C±3°C
Frequency Stability Over Operating Temp. Range (Reference 25°C)	ST	± 15			ppm	@-40~85°C
		± 30				@-40~105°C
		± 50				@-40~125°C
Operating Temperature	Topr	-40	25	125	°C	
Load Capacitance	CL	8 , 10 , 12 or specify			pF	
Drive Level	DL	-	100	300	uW	
Equivalent Series Resistance	ESR	-	-	180	Ohm	8~12MHz
		-	-	100		12~20MHz
		-	-	60		20~30MHz
		-	-	30		32~62.4MHz
Aging	-	± 3			ppm	1st Year
		± 15				15th Year

Note : The table shows common spec. if you have special spec. requirement , please feel free to contact our salesperson.

● **Dimensions**



(Unit : mm)