



- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
  2. Voltage Rating: 250V AC, DC
  3. Temperature Range: -25°C~ +85°C
  4. Contact Resistance: 20mΩ Max
  5. Insulation Resistance: 1000mΩ Min
  6. Withstanding Voltage: 1000V AC/minute
  7. Material: Wafer Nylon66 UL94-VO  
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XH-2AW-G-XX	2.50	7.50
3	XD-XH-3AW-G-XX	5.00	10.00
4	XD-XH-4AW-G-XX	7.50	12.50
5	XD-XH-5AW-G-XX	10.00	15.00
6	XD-XH-6AW-G-XX	12.50	17.50
7	XD-XH-7AW-G-XX	15.00	20.00
8	XD-XH-8AW-G-XX	17.50	22.50
9	XD-XH-9AW-G-XX	20.00	25.00
10	XD-XH-10AW-G-XX	22.50	27.50
11	XD-XH-11AW-G-XX	25.00	30.00
12	XD-XH-12AW-G-XX	27.50	32.50
13	XD-XH-13AW-G-XX	30.00	35.00
14	XD-XH-14AW-G-XX	32.50	37.50
15	XD-XH-15AW-G-XX	35.00	40.00
16	XD-XH-16AW-G-XX	37.50	42.50

**Ordering Information**

XD - XH - N \*\*\* - G - \*\*

Pin: N=尼龙, AW=铜, AL=铝, AN=铝镍  
Type: 2=2位, 3=3位, 4=4位, 5=5位, 6=6位, 7=7位, 8=8位, 9=9位, 10=10位, 11=11位, 12=12位, 13=13位, 14=14位, 15=15位, 16=16位  
Contact Plating: 8=Sn, 9=镀锡, 0=镀金, 1=镀金, 2=镀金, 3=镀金, 4=镀金, 5=镀金

GENERAL TOLERANCE			制图 DRAWING	09	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	XH (2.50) 单排 弯针	版本 REV.	A
X.XX ±0.20			比例 SCALE		产品料号 PART NO.	XD-XH-NAW-G-XX	单位 UNITS	mm
X.XXX ±0.10			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						