


SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 30mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 650V AC/minute
7. Material: Housing Nylon66 UL94-VO

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XHD-2x2Y-X	2.50	7.50
3	XD-XHD-2x3Y-X	5.00	10.00
4	XD-XHD-2x4Y-X	7.50	12.50
5	XD-XHD-2x5Y-X	10.00	15.00
6	XD-XHD-2x6Y-X	12.50	17.50
7	XD-XHD-2x7Y-X	15.00	20.00
8	XD-XHD-2x8Y-X	17.50	22.50
9	XD-XHD-2x9Y-X	20.00	25.00
10	XD-XHD-2x10Y-X	22.50	27.50
11	XD-XHD-2x11Y-X	25.00	30.00
12	XD-XHD-2x12Y-X	27.50	32.50
13	XD-XHD-2x13Y-X	30.00	35.00
14	XD-XHD-2x14Y-X	32.50	37.50
15	XD-XHD-2x15Y-X	35.00	40.00
16	XD-XHD-2x16Y-X	37.50	42.50
17	XD-XHD-2x17Y-X	40.00	45.00
18	XD-XHD-2x18Y-X	42.50	47.50
19	XD-XHD-2x19Y-X	45.00	50.00
20	XD-XHD-2x20Y-X	47.50	52.50



			GENERAL TOLERANCE	制图 DRAWING	05	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK					产品名称 TITLE
			X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-XHD-2xNY-X	单位 UNITS	mm
			X.XX ±0.20	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10						
1	初版发行		Angle ±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE							