



- SPECIFICATIONS**
1. Current Rating: 1A AC, DC
  2. Voltage Rating: 50V AC, DC
  3. Temperature Range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
  4. Contact Resistance:  $20\text{m}\Omega$  Max
  5. Insulation Resistance:  $100\text{M}\Omega$  Min
  6. Withstanding Voltage: 500V AC/minute
  7. Material: Wafer LCP/NylonUL94V-0  
PIN Phosphoric bronze Tin-plated  
Solder tad Phosphoric bronze Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-GH-2PWT	1.25	3.85	5.75
3	HC-GH-3PWT	2.50	5.10	7.00
4	HC-GH-4PWT	3.75	6.35	8.25
5	HC-GH-5PWT	5.00	7.60	9.50
6	HC-GH-6PWT	6.25	8.85	10.75
7	HC-GH-7PWT	7.50	10.10	12.00
8	HC-GH-8PWT	8.75	11.35	13.25
9	HC-GH-9PWT	10.00	12.60	14.50
10	HC-GH-10PWT	11.25	13.85	15.75
11	HC-GH-11PWT	12.50	15.10	17.00
12	HC-GH-12PWT	13.75	16.35	18.25
13	HC-GH-13PWT	15.00	17.60	19.50
14	HC-GH-14PWT	16.25	18.85	20.75
15	HC-GH-15PWT	17.50	20.10	22.00
16	HC-GH-16PWT	18.75	21.35	23.25

			GENERAL TOLERANCE		制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK					
			X.X	$\pm 0.30$	批 准 APPROVAL		产品名称 TITLE	卧 贴	版本 REV.	A
1			初版发行		比 例 SCALE		产品料号 PART NO.	HC-GH-NPWT	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle		$\pm 3.0^{\circ}$	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1