


PCB LAYOUT

SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Wafer LCP UL94-V0
PIN Brass Tin-plated
Solder pad Brass Tin-plated

| Circuit | Part NO. | Dimensions mm | |
|---------|---------------|---------------|-------|
| | | A | B |
| 2 | HC-HY-2AWT-X | 2.00 | 6.00 |
| 3 | HC-HY-3AWT-X | 4.00 | 8.00 |
| 4 | HC-HY-4AWT-X | 6.00 | 10.00 |
| 5 | HC-HY-5AWT-X | 8.00 | 12.00 |
| 6 | HC-HY-6AWT-X | 10.00 | 14.00 |
| 7 | HC-HY-7AWT-X | 12.00 | 16.00 |
| 8 | HC-HY-8AWT-X | 14.00 | 18.00 |
| 9 | HC-HY-9AWT-X | 16.00 | 20.00 |
| 10 | HC-HY-10AWT-X | 18.00 | 22.00 |
| 11 | HC-HY-11AWT-X | 20.00 | 24.00 |
| 12 | HC-HY-12AWT-X | 22.00 | 26.00 |
| 13 | HC-HY-13AWT-X | 24.00 | 28.00 |
| 14 | HC-HY-14AWT-X | 26.00 | 30.00 |
| 15 | HC-HY-15AWT-X | 28.00 | 32.00 |
| 16 | HC-HY-16AWT-X | 30.00 | 34.00 |

Ordering Information



| | | | GENERAL TOLERANCE | | 制 图 DRAWING | | 深圳市华灿天禄电子有限公司 ShenzhenhuacantianlueELECTRONICS CO., LTD | | | |
|-----------|------------------------|-------------------|-------------------|-------|-------------------|--|--|--------------|--------------|-----|
| | | | DIM | TOL | 审 核 CHECK | | 产品名称 TITLE | HY (2.0) 卧贴 | 版本 REV. | A |
| | | | X.X | ±0.30 | 批 准 APPROVAL | | 产品料号 PART NO. | HC-HY-NAWT-X | 单 位 UNITS | mm |
| 1 | 初版发行 | | X.XX | ±0.20 | 比 例 SCALE | | 材 料 | | 页 次 SHEET | 1/1 |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | X.XXX | ±0.10 | 投 影 Projection | | | | | |
| | | | Angle | ±3.0° | | | | | | |