


- SPECIFICATIONS**
- 1、Current Rating: 3A AC, DC
  - 2、Voltage Rating: 250V AC, DC
  - 3、Temperatuer Range:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
  - 4、Contact Resistance:  $20\text{m}\Omega$  Max
  - 5、Insulation Resistance:  $1000\text{M}\Omega$  Min
  - 6、Withstanding Voltang:  $1000\text{V AC/minute}$
  - 7、Material: Wafer Nylon66, UL94V-0  
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-5264-2A	2.50	7.50
3	HC-5264-3A	5.00	10.00
4	HC-5264-4A	7.50	12.50
5	HC-5264-5A	10.00	15.00
6	HC-5264-6A	12.50	17.50
7	HC-5264-7A	15.00	20.00
8	HC-5264-8A	17.50	22.50
9	HC-5264-9A	20.00	25.00
10	HC-5264-10A	22.50	27.50
11	HC-5264-11A	25.00	30.00
12	HC-5264-12A	27.50	32.50

**PCB LAYOUT**

		GENERAL TOLERANCE		制图 DRAWING	 <b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO.,LTD			
		DIM	TOL	审核 CHECK				
		X.X	$\pm 0.30$	批准 APPROVAL	产品名称 TITLE	5264 直针	版本 REV.	A
1		初版发行		比例 SCALE	产品料号 PART NO.	HC-5264-NA	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	$\pm 3.0^{\circ}$	投影 Projection	材料 MATERIAL	页次 SHEET	1/1