








- NOTES:(Unless otherwise specified)
1. Dimension shall be interpreted per ANSI Y14.5M.
 - 2.Current Rating:0.5 A Per pin.
 - 3.Voltage Rating: 50V AC/DC
 - 4.Working Temperature: -55°C to +125°C.



Pin	A	B	C	D	E	F
10 Pin	4.60	2.00	2.70	3.10	4.10	5.60
14 Pin	5.60	3.00	3.70	4.10	5.10	6.60
20 Pin	7.10	4.50	5.20	5.60	6.60	8.10
30 Pin	9.60	7.00	7.70	8.10	9.10	10.60
32 Pin	10.10	7.50	8.20	8.60	9.60	11.10
36 Pin	11.10	8.50	9.20	9.60	10.60	12.10
40 Pin	12.10	9.50	10.20	10.60	11.60	13.10
50 Pin	14.60	12.00	12.70	13.10	14.10	15.60
60 Pin	17.10	14.50	15.20	15.60	16.60	18.10
80 Pin	22.10	19.50	20.20	20.60	21.60	23.10
100 Pin	27.10	24.50	25.20	25.60	26.60	28.10



Ordering Information

HC-PBB12 ** (*) - NDS - 0.5V - P - 03

Type NB=母座 NC=母座 High (H) 台高 (3.0)~3.00mm No. of Pins 10~120Pin Nature DS=Female (母座) PITCH 0.5V=0.5mm Post (焊耳) 3.5/4.0/5.0mm

3	BRASS	100u" MIN.TIN PLATED UNDER PLATING; 50u" NIKEL PLATED
2	PHOSPHOR BRONZE	CONTACT AREA: GOLD PALTED LEAD AREA: GOLD FLASH UNDER PLATING; 50u" NIKEL PLATED
1	POLYAMIDE	UL94V-0, BLACK/NATURE
NO.	MATERIAL	FINISH.REMARKS

GENERAL TOLERANCE		制图 DRAWING
DIM	TOL	审核 CHECK
X.X	±0.30	批准 APPROVAL
X.XX	±0.20	比例 SCALE
X.XXX	±0.10	投影 Projection
Angle	±3.0°	

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	BTB 0.5 立贴 母座 带焊耳	版本 REV.	A
产品料号 PART NO.	HC-PBB12NB-NDS-0.5V-03	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1