

特性:Specifications;

电器:Electyical:

接触阻抗:Contact Resistance

30 millionms MAX

耐电压:Dielectyic Withstanding Voltage:

500v AC AT Sea Level

绝缘阻抗:Insulation Resistance:

1000 MEGA ohms MLN





机构:Machanical:

接合为:Mating Force;

4.0 KG MAX 最大4Kg

拔出力:Unmating Force;

0.7KG MIN.最少0.7KG



PART NO	H
U-A-24DD-Y-7	13.00
U-A-24DD-Y-8	13.70
U-A-24DD-Y-9	15.00

Recommended PCB Layout

③	Base	—	1	NYLON	White
②	Terminal	—	4	Phosphor Bronze	Ag Plated
①	Housing	—	1	SPCC/Phosphor Bronze	Ni Plated
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING

APPROVALS			DATE				
DRAWN	JIANKUN.LU		2015.03.18				
CHECKED					PART NO.		
APPROVALS					UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE			30~以上	±0.30	ANGLE	DRAWING NO.	SHEET 1 OF 1
			10~30	±0.25			
			5~10	±0.20			
			~ 5	±0.15			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—