


Specifications:
 规格:
 1.Voltage rating:250VAC/DC
 额定电压: 250V AC/DC
 2.Current rating:5A AC/DC
 额定电流: 5A AC/DC
 3.Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 4.Temperature range: -55°C~+105°C
 温度范围: -55°C~+105°C
 5.Insulation resistance:500MΩ MIN
 绝缘电阻:500MΩ MIN
 6.Contact resistance:30mΩ Max
 接触电阻: 30mΩ Max
 Material:
 材料:
 7.Rubber core:PBT+G/F UL94V-0
 胶芯: PBT+C/F UL94V-0
 8.The iron shell:Steel ; Tin Plating
 铁壳: 钢 ; 镀锡
 9.Terminal:Brass
 端子: 黄铜

X01 XX F X X X X L
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series NO.
- ② Row No.Pin No.XX-09;15;25;37
- ③ Welding Board Angle :F-Female
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Category: 1:Gold 1u ;2:Gold 2u; 3:Gold 3u ;4:Gold 5u; 5:Gold 15u; 6:Gold 30u ;7:Terminal half- Gold Bright Tin;8: Terminal half- Gold 2u Bright Tin 9: Terminal half- Gold 3u Bright Tin;10: Terminal half- Gold 5u Bright Tin 11: Terminal half- Gold 15u Bright Tin;12: Terminal half- Gold 30u Bright Tin 13: Terminal half- Gold Matte Tin;14: Terminal half- Gold 2u Matte Tin 15: Terminal half- Gold 3u Matte Tin; 16: Terminal half- Gold 5u Matte Tin 17: Terminal half- Gold 15u Matte Tin;18: Terminal half- Gold 30u Matte
- ⑥ TinColor:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 5:TYPE-5
- ⑧ L: Stitching lengthening



NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	16.35	24.99	30.80	19.28
15	24.75	33.32	39.20	27.51
25	38.35	47.04	53.05	41.28
37	54.75	63.50	69.40	57.71

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: D-SUB
DWN		VIEW:	PART NO.: X01XXFXXXXL
CHKD		UNIT: mm/in	DWG NO.: X-X01XXFXXXXL
APPD		SIZE: A4	WEIGHT SHEET REVISION
			1/1 A0