



300V 15A
Poles: 2-22P
Pitch: 5.0mm(.197")/5.08mm(.200")
Materials
Housing: PA66(UL 94V-0)
Solder Pin: Brass, Tin Plated.
Nut: M2.5, Brass

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance
				X, ±0.2 X, ° ±2°
				.X ±0.1 .X° ±1°
				.XX ±0.05 .XX° ±0.5°
				.XXX ±0.01
图名/Title				文件编号/File No.
XY2500VBS-5.0				
VDS-5.08				页序/Sheet
备注/Remark				单位/units: mm



XINLAIYA ELECTRONIC CO., LTD