



一、 MATERIAL:

- 1.Insulator:PBT+30%Glass Fiber (UL94V-0)
- 2.Contact:Brass
- 3.Contact Plated:Glod Flash over Tin Or Glod Plated Or Tin Plated
- 4.Shell:Stell,Nickel Plated

二、 SPECIFICATION:

- 1.Current Rating:5 AMPS
- 2.Insulation Resistance: 1000MΩ MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

L&X深圳市连欣科技有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*	DRAWN BY :	DATE :	PART NAME:
			2014-02-23
 UNIT: mm [inch]	CHECKED BY:	DATE :	PART NO. XDDB-1510-1445
	马跃	2014-02-23	MOLD NO.
SCALE:1:1	APPROVED BY:	DATE :	DRAW NO: VGA1909101445
SIZE: A4	柯南	2014-02-23	SHEET NO. 1 OF 1