



版本 REV.	變更內容 MODIFICATION	日期 DATE
A		







ELECTRICAL CHARACTERISTICS:
 CONTACT CURRENT RATING : 1.5AMPERES.
 DIELECTRIC WITHSTANDING VOLTAGE : AC 500V R.M.S.
 INSULATION RESISTANCE : 1000 MEGOHMS MINIMUM AT DC 500V.
 CONTACT RESISTANCE : 30 MILLIOHM MAXIMUM.
 OPERATING TEMPERATURE : -55?T0+105?


MECHANICAL CHARACTERISTICS: CONTACT INSERTION FORCE :3.57KG MAXIMUM.
 CONTACT SEPARATION FORCE :1.0KG MINIMUM.

MATERIALS:
 HOUSING:PA9T GREEN
 CONTACT:PHOSPHOR COPPER T=0.25?0.01mm.
 SHELL: copper,T=0.30?0.02mm;

CONTACTS:GOLD FLASHED 1U",3U",5U",10U",15U",30U".
 END OF NI-50U"MIN
 SHELL: NICKEL PLATED OVER 30~100U" MIN.



P.C.B LAYOUT



深圳市连欣科技有限公司

單位 UNIT	MM	製圖 DRAWN	圖號 DWG NO.	XDBF-0050-01		
未注公差 TOLERANCE UNSPECIFIED		設計 DESIGN	模號 DWG NO.	品名 TITLE		
X.X	±0.30	審核 CHECKED	比例 SCALE	大电流USB4F四脚平口		
X.XX	±0.20			1:1	版本 REV.	A
X.XXX	±0.10	核准 APPROVE	角法 PROJ.	CUSTOMER DRAWING		
X*	±5°			⊕		
X.X*	±2°					