




1 2 3 4 5 6 7

A



B



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN


原材料: Material:

1. 塑胶: Housing:
High Temperature Thermoplastics,
PBT/LCP White/Black
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails
2. 外壳: Shell:
Nickel Plating

D



E

L&X 深圳市连欣科技有限公司 http://www.szlianxinkeji.com/		图号 (DWG NO)	4C	单位 (UNIT): MM
		版本 (REV)	A/1	比例 (SCALE) 1:1
品名 (ITEM NO) USB A/F 180° DIP长体直脚(13.7)母座		日期 (DATE)	2009. 12. 17	
		设计 (DESIGN)	陈钦虎	
料号 (PART NO) XUBF-0218-0139		审核 (CHECKED)		未注公差 TOLERANCE UNSPECIFIED X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 X° ±5° X.X° ±2°
模号 (MODEL NO) UB003G		核准 (APPROVED)		

1 2 3 4 5 6 7