



1 2 3 4 5 6 7


A

A



B

B



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating  
1.5A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
1000MEGA ohms MIN

原材料: Material:

1. 塑胶: Housing:  
High Temperature Thermoplastics,  
PBT/LCP White/Black
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:


1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Tails
2. 外壳: Shell:  
Nickel Plating

C

C

D

D



E

E

<b>L&amp;X 深圳市连欣科技有限公司</b> TEL: 0755-33978030 FAX: 0755-32937438		图号 (DWG NO)	4C	单位 (UNIT): MM
		版本 (REV)	A/1	比例 (SCALE) 1:1
品名 (ITEM NO)	USB A/F 180° DIP长体改脚(15.0)母座	日期 (DATE)	2009. 12. 17	未注公差 TOLERANCE UNSPECIFIED X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 X° ±5° X.X° ±2°
料号 (PART NO)	XUDF-0218-0151	设计 (DESIGN)	陈钦虎	
模号 (MODEL NO)	UB001G	审核 (CHECKED)		
		核准 (APPROVED)		

1 2 3 4 5 6 7