



适用线路板

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺格、裂纹等现象。
2. 温度范围:  $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$
3. 额定电压: 100V, AC/DC.
4. 接触电阻:  $\leq 20\text{m}\Omega$ .
5. 绝缘电阻:  $\geq 1000\text{M}\Omega$ .
6. 额定电流: 3A, AC/DC.

序号	项目	描述	备注
1	翻膜	ICP	
2	端子	黄铜	
3	焊片	黄铜	
4	盖子		

CKT	DIM A	DIM B	DIM C
2	2.00	4.80	7.95
3	4.00	6.80	9.95
4	6.00	8.80	11.95
5	8.00	10.80	13.95
6	10.00	12.80	15.95
7	12.00	14.80	17.95
8	14.00	16.80	19.95
9	16.00	18.80	21.95
10	18.00	20.80	23.95
11	20.00	22.80	25.95
12	22.00	24.80	27.95
13	24.00	26.80	29.95
14	26.00	28.80	31.95
15	28.00	30.80	33.95
16	30.00	32.80	35.95
17	32.00	34.80	37.95
18	34.00	36.80	39.95
19	36.00	38.80	41.95
20	38.00	40.80	43.95

深圳市连欣科技有限公司

规格 (mm)  
WAFER P12.00MM 立式贴片式SMT

料号 (MFG NO)

XDMF-0221-44P

比例 (SCALE)

1:1

厚度 (UNIT)  
mm



张数 (SHEET)  
1 OF 1

SIZE  
A4

REV  
A

一般公差 (TOLERANCE)  
X ±.50 XX ±.10  
X ±.20 XXX ±.05  
ANGLES ±1°