

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/13/06	
A		REDRAWN	1/10/14	AY/LL



SPECIFICATIONS:

Material:
 Insulator: Nylon 66 UL 94V-0
 Insulator color: White
 Electrical:
 Operating voltage: 250 V AC/DC
 Current rating: 3A AC/DC
 Insulation resistance: 1,000Mohms Min.
 Dielectric withstanding voltage: 800V AC for 1 MIN.
 Temperature Rating:
 Operating temperature: -25°C to +85°C
 Environmental:
 Lead free, RoHS compliant



Positions: 2 thru 15
 A = .098 [2.50] x No. of Spaces
 B = .098 [2.50] x No. of Spaces + .169 [4.30]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES HOLES			
.X ± .10	Ø.X ± .10	TITLE WIRE TO BOARD PITCH: 2.5MM CRIMP HOUSING	
.XX ± .020	Ø.XX ± .015		
.XXX ± .015	Ø.XXX ± .010		
APPROVALS		DATE	
DRAWN	LFJ	4/13/06	
CHECKED			
APPROVED			
SIZE X	PART NO. 25CH-C-XX	REV. A	
REF: S00016T	SCALE: NTS	SHEET 1 OF 1	

6

5

4

3

2

1