


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/29/10	A.D.M.



NOTES:

MATERIALS:

1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
2. CONTACT & FERRULE = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
3. GASKET = SILICONE RUBBER 45-55 DUROMETER DOW CORNING SILASTIC 250.
4. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
5. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

1. CONTACT & WIRE ADAPTOR = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.
2. ALL OTHER METAL PARTS = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON	DWN:	A.D.M.	DATE	09/29/10	
	CHKD:	D.N.	DATE	09/29/10	
DECIMAL	ANGLE	APVD:	J.M.	DATE	09/29/10
REFERENCE:	MATERIALS & FINISHES: SEE NOTES				
ORIGINATOR: A.D.M. DATE: 09/29/10					



Property of Radiall
This document cannot be reproduced or communicated to a third party without prior written permission of RADIALL.

**BNC STRAIGHT JACK
BULKHEAD REAR MOUNT CLAMP
TYPE FOR RG316 & SIMILAR CABLES**

SIZE	FSCM NO.	DWG NO.	REV
A	19505	6501-1051-003	A
SCALE	THIRD ANGLE PROJECTION		SHEET 1 OF 1
5:1			

6501-1051-003