





Rev	AWO #	Description	Date	Appr
-		RELEASED	10/10/07	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:
 Material: Insulator: PBT, glass reinforced, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Plating: Gold
 Flash over Nickel underplate overall

Electrical:
 Operating voltage: 250 VAC max
 Current rating: 3 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 5,000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1,000 VAC for 1 minute
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant

Positions: 1 thru 40
 A = .100 [2.54] x No. of Positions
 B = .100 [2.54] x No. of Positions - 1

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]		TITLE RIGHT ANGLE, HIGH PROFILE, GOLD PLATED	
TOLERANCES: EXCEPT AS NOTED		.100 [2.54] SINGLE ROW PIN HEADER	
INCHES		SIZE	
.X ± .10	ØXX ± .10	X	PART NO. PH1RA-XX-UA
.XX ± .020	ØXXX ± .015		REV.
.XXX ± .015	ØXXXX ± .010		
APPROVALS		SCALE: NTS	
DRAWN	SS	DATE: 10/10/07	
CHECKED		SHEET 1 OF 1	
APPROVED			

