



SPECIFICATIONS
 Current Rating: 2.0AMP
 Contact Resistance: 10mΩMax
 Dielectric Strength: Min 1000V RMS
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Clip (4/6 finger): Becu (C17200)
 Accepted Pin: $\phi 0.40$ to 0.60mm
 Insulator Material: Polyester (UL94V-0)
 Standard: PPS
 Soldering temperature: $260^\circ\text{C} \pm 5'$ 5S

Ordering Information

XDM 200 C - * - N - Z - * - **

Round Pin 圆针	No. of Rows 1=Single Row 2=Dual Row	No. of Pins 01-40 Pin	Type Z=直针 W=弯针 S=插脚	Length 长度	Contact Plating G0: Gold Flash G1: 1μ' Gold G2: 3μ' Gold G3: 5μ' Gold G4: 10μ' Gold G5: 15μ' Gold G6: 30μ' Gold S0: Gold Flash/Tin S1: Tin
-----------------	---	--------------------------	------------------------------	--------------	---

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 Shenzhen Xunda Technology Co., Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	2.00 双排 圆直排母 L7.4 (塑高2.8)	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XDM200C-2-N-Z-2.8-XX	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					