

RP73D2A10KBTG

✓ ACTIVE

Holsworthy | Holsworthy RP73


TE Internal #: 7-1879276-3

10K  $\Omega$ , Thin Film, Precision Resistor, .1 %, 2 Termination, 0805, Cut Tape Length, .125 W,  $\pm 15$  ppm/ $^{\circ}\text{C}$ , Solder, Height .022 in [.55 mm], Holsworthy RP73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**  
Number of Terminations: **2**  
Package Size Code: **0805**  
Packaging Method: **Cut Tape Length**  
Passive Component Tolerance: **.1 %**

Features

Product Type Features

Resistor Type	Precision Resistor
Package Size Code	0805
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	150 V
Passive Component Tolerance	.1 %
Resistance Class	1k $\Omega$ – 1M $\Omega$
Resistance Value	10K $\Omega$
Power Rating	.125 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]
Product Width	1.25 mm[.049 in]



Usage Conditions

Temperature Coefficient	$\pm 15$ ppm/ $^{\circ}\text{C}$
-------------------------	----------------------------------

Packaging Features

Packaging Method	Cut Tape Length
------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260 $^{\circ}\text{C}$

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 9-1879252-4 RP 2B 10R 0.1% 15PPM CUT LENGTH	 TE Part # 5-1879267-0 RP 2B 1M0 0.1% 15PPM 1K RL	 TE Part # 2-1879747-4 RP 1J 110K 0.1% 15PPM CUT LENGTH	 TE Part # 5-1879743-7 RP 1J 18R2 0.1% 15PPM CUT LENGTH
---	--	--	--

RP73D2A10KBTG

10K  $\Omega$ , Thin Film, Precision Resistor, .1 %, 2 Termination, 0805, Cut Tape Length, .125 W,  $\pm 15$  ppm/ $^{\circ}$ C, Solder, Height .022 in [.55 mm], Holsworthy RP73



TE Part # 2-1879279-6

RP 2A 75K 0.1% 15PPM 1K RL

Also in the Series | Holsworthy RP73

Surface Mount Resistors(4556)

Customers Also Bought

TE Part #5-1622820-5

3520 5R6 5%

TE Part #1571983-1

GDH02S04=DIP SWITCH

TE Part #1676142-2

RN 0805 100K 0.1% 10PPM 1KRL

TE Part #102387-3

16 MODIV HSG COMP DR .100 POL

TE Part #825433-4

MOD 2 PINHDR 1X4 P.

TE Part #1-111446-6

16 UNIV I/O, NO EARS, LEAD FREE

TE Part #1623198-1

CRG0805 1% 33R

TE Part #2311763-1

AMPL REC, HD22, R/A, 15P, S/L

TE Part #1676407-2

RN 0805 681R 0.1% 10PPM 1KRL



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_7-1879276-3\_BA.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_7-1879276-3\_BA.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_7-1879276-3\_BA.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350\_PASSIVE\_COMPONENT

English

RP73-0915

English

8-1773459-4\_POWER\_FILTERING\_AND\_RESISTIVE\_SOLUTIONS\_FOR\_ELEVATORS\_AND\_ESCALATORS

English