




Date	SYM	REVISION RECORD	AUTH	DR.	CK.
4/22/06	A	Added "ROHS COMPLIANT"	T.B.	B.S.	
3/10/17	B	ADDED MOUNTING INSTRUCTION	T.B.	B.S.	



9 VOLT SNAPS TYPE SHOWN




SPECIFICATION:

1. MATERIAL:

HOUSING : BLACK POLYPROPYLENE, PP-1040
 FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959
 TEMPERATURE RANGE: -10°C to +100°C
 RIVETS: BRASS, NICKLE PLTD.
 SPRING: SPRING STEEL, NICKLE PLTD.
 9VOLT SNAPS: BRASS, NICKLE PLATED
 CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER
 EIA-540J000
 ROHS 2 COMPLIANT

MOUNTING INSTRUCTION:

USE 4-40 MACHINE SCREWS OR EYELETS OR EQUIVALENT.
 ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.

Tolerance (Except as noted)	 Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735	Scale	Drawn By B.S.
		1.5=1	Approved By T.B.
decimal ±.5 (.020)	Title SIX "C" CELL HOLDER WITH 9V SNAPS		
Fractional ± .8 (.030)		Date 03/10/17	Drawing Number BH26CSF
Angular ± 3°			