Product data sheet Characteristics

XS2M08PC410D

inductive sensor XS2 M8, L61mm, stainless, Sn2.5mm, 12..24VDC, M12





Main

Range of Product	Telemecanique Inductive proximity sensors XS
Series name	General purpose
Sensor Type	Inductive proximity sensor
Sensor name	XS2
Sensor design	Cylindrical M8
Size	61 mm
Body type	Fixed
Detector flush mounting acceptance	Non flush mountable
Material	Stainless steel
Type of output signal	Discrete
Wiring Technique	4-wire
[Sn] nominal sensing distance	0.10 in (2.5 mm)
Discrete output function	1 NO + 1 NC
Output circuit type	DC
Discrete output type	PNP
Electrical connection	Male connector M12, 4 pins
[Us] rated supply voltage	1224 V DC reverse polarity protection
Switching capacity in mA	<= 200 mA overload and short-circuit protection
IP degree of protection	IP67 conforming to IEC 60529

Complementary

The state of the s	110
Thread type	M8 x 1
Detection face	Frontal
Front material	PPS
Enclosure Material	Stainless steel 303
Operating zone	0.000.08 in (02 mm)
Differential travel	115% of Sr
Status LED	Output state 1 LED yellow)
Supply voltage limits	1036 V DC
Switching frequency	<= 5000 Hz
Maximum voltage drop	<2 V closed)
Current consumption	010 mA no-load
Maximum delay first up	5 ms
Maximum delay response	0.1 ms
Maximum delay recovery	0.1 ms
Marking	CE
Threaded length	1.42 in (36 mm)
Length	2.40 in (61 mm)
Net Weight	0.06 lb(US) (0.025 kg)

Environment

Product Certifications	UL CSA
Ambient air temperature for operation	-13158 °F (-2570 °C)
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)
Vibration resistance	25 gn +/- 2 mm 1055 Hz)IEC 60068-2-6
Shock resistance	50 gn 11 ms IEC 60068-2-27

Ordering and shipping details

Category	22486 - SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	3389110550146
Nbr. of units in pkg.	1
Package weight(Lbs)	1.16 oz (33 g)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	1.65 in (4.2 cm)	
Package 1 width	2.60 in (6.6 cm)	
Package 1 Length	3.74 in (9.5 cm)	


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EV RoHS Declaration
Mercury free	Yes
RoHS exemption information	₫Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	☐ End Of Life Information

Contractual warranty

Warranty	18 months

Dimensions




(1) LED

XS2M08PC410D

Minimum Mounting Distances


Side by side



e (1) 10 mm/0.39 in.

≥


Face to face



e (2) 30 mm/1.18 in.

≥


Facing a metal object



e (3) 7.5 mm/0.30 in.

≥ `

Mounted in a metal support



d ≥ 24 mm/0.94 in.


h ≥ 5 mm/0.20 in.

Product data sheet Connections and Schema

XS2M08PC410D

Wiring Schemes

PNP 4-wire



BU: Blue BN: Brown BK: Black WH: White