## 8501RS43P14V20

Plug in relay, Type R, miniature, 1 HP at 277 VAC, 15A resistive at 120 VAC, 11 blade, 3PDT, 3 NO, 3 NC, 120 VAC coil



## Main

Product range	8501R
Product type	Miniature Relay
Relay Type	Standard

Complementary

Complementary		
Mounting type	Socket	
Contact composition	3PDT	
[Uc] control circuit voltage	120 V AC	
Pilot light	Green indicator relay energised LED	
Manual operator	Without test button	
Horsepower rating	0.5 120 V AC 1 277 V AC	
Breaking capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 10 A 120 V AC resistive control circuit UL 508 6.67 A 277 V AC resistive control circuit UL 508 10 A 28 V DC resistive control circuit UL 508	
Maximum switching voltage	300 V AC 30 V DC	
Contact material	Silver alloy, gold flashed	
Operating time	20 ms - pick-up 20 ms - drop-out	
Shape of pins	Spade	
For use with	8501NR43	
Height	1.07 in (27.3 mm)	
Width	1.20 in (30.6 mm)	
Depth	1.65 in (41.8 mm)	

## Environment

Ambient temperature range - operational	-40131 °F (-4055 °C)
Product certifications	UL Listed UL Recognized CSA CE

## Ordering and shipping details

eraering and empping actains		
Category	21143 - 8501 R	
Discount Schedule	CP2	
GTIN	785901137139	
Nbr. of units in pkg.	1	
Package weight(Lbs)	2.08 oz (58.967 g)	

Returnability	Yes	
Country of origin	CN	
Packing Units		
Unit Type of Package 1	PCE	
Package 1 Height	1.30 in (3.302 cm)	
Package 1 width	1.70 in (4.318 cm)	
Package 1 Length	1.90 in (4.826 cm)	
Offer Sustainability		
Sustainable offer status	Green Premium product	
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
REACh Regulation	☑ REACh Declaration	
REACh free of SVHC	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS  Declaration	
Toxic heavy metal free	Yes	
Mercury free	Yes	
RoHS exemption information	₫Yes	
China RoHS Regulation	China RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
Contractual warranty		
Warranty	18 months	