



Poles	04	06	08	10	12	14	16	18	20	22	24	26
Dim L	8.5	12.0	15.5	19.0	22.5	26.0	29.5	33.0	36.5	40.0	43.5	47.0
Dim B	3.50	7.00	10.5	14.0	17.5	21.0	24.5	28.0	31.5	35.0	38.5	42.0
TOL	±0.15						±0.20					
Poles	28	30	32	34	36	38	40	42	44	46	48	
Dim L	50.5	54.0	57.5	61.0	64.5	68.0	71.5	75.0	78.5	82.0	85.5	
Dim B	45.5	49.0	52.5	56.0	59.5	63.0	66.5	70.0	73.5	77.0	80.5	
TOL	±0.25						±0.30					

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.6.08	Add UL standard	Jacke
△	2009.6.08	The current rating and operating temperature are changed	Jacke
△	2009.6.08	Corrected dimension △ from 2.3mm to 2.5mm	Jacke
△	2010.01.22	The demension is changed from 1.60mm to 1.10mm	Jacke
△	2010.01.22	The demension is changed from 0.40mm to 0.20~0.30mm	Jacke
△	2010.03.31	The material is changed from Brass to Copper	Jacke
△	2010.04.01	The design is changed	Jacke

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- Material**
- △ Item (a) Short contact pin: Copper Tin plated
 - Item (b) Long contact pin: Copper Tin plated
 - Item (c) Terminal (housing): Thermoplastic (UL94V-0)
 - Item (d) Terminal (cover): Thermoplastic (UL94V-0)
- Electrical**
- Voltage rating: 300VAC
 - △ ● Current rating: 8A
 - Wire range:
 - Solid wire(AWG):
 - Stranded wire(AWG):
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - △ ● Soldering temperature: 250°C±10°C/5 Sec
 - △ ● Safety Approval: us

VL xx 1 3 x 1 xxxx G

- G: Pb<40000ppm
- | | | |
|------------------|---------------------|----------------------|
| POLES | COLOR | 000 0 "@ logo |
| 04 2x2 CONTACTS | 0 Black (RAL9005) | 000 A "ANY" logo |
| 06 2x3 CONTACTS | 2 Red (RAL3001/D) | Any special item by |
| ... | 3 Orange(RAL2011/P) | customer request, |
| 48 2x24 CONTACTS | 4 Yellow(RAL1018/A) | please contact sales |
| | 5 Green(RAL6018/T) | department. |
| | 6 Blue (RAL5015/A) | |
| | 8 Grey(RAL7035/D) | |

ANYTEK				CUSTOMER COPY			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		VL-3.5mm Right -Angle Series "B Type"					
PART NO.		VLxx13x1xxxxG			DWG NO.		8VL0402
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Jacke	Jacke				X. ±0.50
		2010.03.31	2010.01.22				X.X ±0.30
							X.XX ±0.10
							X° ±1°
					SHEET: 01/01		REV.: D