


Date	SYM	REVISION RECORD	AUTH	DR. CK.
10/03/14	B	REDRAWN IN AUTOCAD UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.




158.20 [6.22]

∅4.44 [∅0.17]

8.26 [0.32]

8.26 [0.32]

71.5 [2.83]




57.50 [2.26]

NOTES:

1. MATERIAL:

HOUSING : BLACK POLYPROPYLENE  
 FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959  
 TEMPERATURE RANGE: -10°C to +100°C  
 RIVETS: BRASS, NICKEL PLATED.  
 SPRING: SPRING STEEL, NICKEL PLATED.  
 CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER  
 EIA-540J000

ROHS 2 COMPLIANT.

 <b>Memory Protection Devices, Inc</b> 200 Broad Hollow Road, Farmingdale, New York 11735	Scale	
	Drawn By B.S.	Approved By T.B.
Tolerance (Except as noted)	decimal	
	±.5 (.020)	
Fractional	Title	
± .8 (.030)	TEN "D" CELL HOLDER WITH WIRE LEADS	
Angular	Date	Drawing Number
± 3°	10/03/14	BH510DW