ZB5AA3TQ

22mm push button, Harmony ZB5, plastic base, non illuminated momentary push button, green, bulk packed 100





Main

Range of Product	Harmony XB5
Product or Component Type	Head for non-illuminated push-button
Device short name	ZB5
Bezel material	Dark grey plastic
Mounting diameter	0.87 in (22 mm)
Head type	Standard
Sale per indivisible quantity	10
Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	Green flush, unmarked

Complementary

CAD overall width	1.14 in (29 mm)	
CAD overall height	1.14 in (29 mm)	
CAD overall depth	1.10 in (28 mm)	
Mechanical durability	10000000 cycles	
Station name	XALD 15 cut-outs XALK 25 cut-outs	
Electrical composition code	C1 9 single front mounting C2 9 single and double front mounting C11 3 single front mounting C15 1 single front mounting SF1 3 single front mounting SR1 3 single rear mounting	

Environment

Protective treatment	TH
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient Air Temperature for Operation	-40158 °F (-4070 °C)
Overvoltage category	Class II IEC 60536
IP degree of protection	IP66 IEC 60529 IP67 IP69 IP69K
NEMA degree of protection	NEMA 13 NEMA 4X
Resistance to high pressure washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m
IK degree of protection	IK03 IEC 50102
Standards	JIS C8201-5-1 UL 508 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-1 JIS C8201-1

Product Certifications	DNV	
	GL	
	UL Listed	
	CSA	
	BV	
	LROS (Lloyds register of shipping)	
Shock resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27	
	50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	
Vibration resistance	5 gn 2500 Hz)IEC 60068-2-6	

Ordering and shipping details

ordering and ompping detaile	
Category	22467-PUSHBUTTONS,22MM(PLASTIC) NEW
Discount Schedule	CS2
GTIN	3389110884401
Nbr. of units in pkg.	1
Package weight(Lbs)	0.71 oz (20.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE	
Package 1 Height	2.13 in (5.4 cm)	
Package 1 width	1.34 in (3.4 cm)	
Package 1 Length	1.73 in (4.4 cm)	
Unit Type of Package 2	CAR	
Number of Units in Package 2	100	
Package 2 Weight	7.05 oz (200 g)	
Package 2 Height	2.13 in (5.4 cm)	
Package 2 width	1.34 in (3.4 cm)	
Package 2 Length	1.73 in (4.4 cm)	

Offer Sustainability

Onor Guotamability	
Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	☑ China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	[™] End Of Life Information

Contractual warranty

ontractal manary	
Warranty	18 months