

公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50

材料及电镀


- ①. 塑件主体: PA66, UL94V-0
- ②. 夹子: 磷青铜, 镀镍
- ③. 方盒: 黄铜, 镀镍
- ④. 塑件盖板: PA66, UL94V-0
- ⑤. 螺丝: M2.0, 钢, 镀锌, 一字槽

电气性能

额定电压: 300V
 额定电流: 8A
 接触电阻: 20mΩ (Max)
 绝缘电阻: 500MΩ \DC500V
 耐电压: AC1600V\1Min
 使用线径: 28-16AWG 1.5mm²

机械性能

温度范围: -40℃ ~ +105℃
 瞬时温度: +250℃ 5秒
 扭力: 0.2Nm (1.77Lbin)
 剥线长度: 6-7mm



Ordering Information

HC15EDG		*	*	-	*	-	NP	-	*
Type	Pitch	No. of Poles	No. of Pins	Colour					
□ 直插 □ 带耳 □ 带脚	2.54=2.54mm 3.5=3.50mm 3.81=3.81mm 5.08=5.08mm 7.62=7.62mm	2-24Pin 2P=2Pin 3P=3Pin	V=Green L=Blue O=Orange R=Red B=Black GR=Grey						

			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD				
			DIM	TOL	审核 CHECK		产品名称 TITLE		3.81 单排 插拔式 带螺丝 接线端子 母座	版本 REV.	A
			X.X	±0.50	批准 APPROVAL		产品料号 PART NO.		HC15EDGKM-3.81-NP-V	单位 UNITS	mm
			X.XX	±0.30	比例 SCALE		材料 MATERIAL			页次 SHEET	1/1
			X.XXX	±0.10	投影 Projection						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°								