

1.材料和电镀\Materials and Finishes:



外壳\Body - 黄铜\Brass,镀三元合金\Tri-matel plating  
 内导体>Contact - 铍铜\Beryllium copper,镀金\Gold plating  
 绝缘体\Insulator - 聚四氟乙烯\Teflon,本色\Natural  
 压套\Tube - 黄铜\Brass,镀三元合金\Tri-matel plating




2.电气性能\Electrical:

A.特性阻抗\Impedance:50 Ohm  
 B.使用频率\Frequency range:DC-10GHz  
 C.介质耐压\Breakdown voltage:1500V rms  
 D.绝缘电阻\Insulation resistance:5000 MΩ

3.机械性能\Mechanical:

A.使用寿命\Durability:500 cycles



技术详询 139-7514-5315 			版次	V2.0	比例	2.5:1	料号	CT10.1.23
			第一角法				规格	N-KFD V2.0
设计	JAT	2024.01.05	1.未注公差按ISO2768-1(m) 2.去尽毛刺C0.13max 3.各圆同轴度Ø0.1max				名称	N型母头穿墙式四孔法兰
审核	DF	2024.01.05						
批准	DF	2024.01.05						
*尺寸为重要尺寸						单位	mm	 深圳成泰电子有限公司 www.cntitle.net