

1.材料和电镀\Materials and Finishes:

外 壳\Body - 黄铜\Brass,镀金\Gold plating
 内导体>Contact - 铍铜\Beryllium copper,镀金\Gold plating
 绝缘体\Insulator - 聚四氟乙烯\Teflon,本色\Natural

2.电气性能\Electrical:


A.特性阻抗\Impedance:50 Ohm
 B.使用频率\Frequency range:DC-6GHz
 C.介质耐压\Breakdown voltage:750V rms
 D.绝缘电阻\Insulation resistance:5000 MΩ




3.机械性能\Mechanical:

A.使用寿命\Durability:500 cycles
 B.中性盐雾\Salt spray:72 hours



建议开孔尺寸



			版次	比例	2.5:1	料号	CT6.1.72
			第一角法			规格	MCX-KHD
技术详询 139-7514-5315			1.未注公差按ISO2768-1(m) 2.去尽毛刺C0.13max 3.各圆同轴度Ø0.1max			名称	MCX母头 (PCB立式焊接)
设计	JAT	2024.01.06	*尺寸为重要尺寸			 深圳成泰电子有限公司 www.cntitle.net	
审核	DF	2024.01.06					
批准	DF	2024.01.06					
			单位	mm			