

1.材料和电镀\Materials and Finishes:

外壳\Body - 黄铜\Brass,镀三价黑铬\Trivalent chromium plating

内导体>Contact - 铍铜\Beryllium copper,镀金\Gold plating

绝缘体\Insulator - 聚四氟乙烯\Teflon,本色\Natural

2.电气性能\Electrical:

A.特性阻抗\Impedance:50 Ohm



B.使用频率\Frequency range:DC-6GHz





C.介质耐压\Breakdown voltage:1500V rms

D.绝缘电阻\Insulation resistance:5000 MΩ

3.机械性能\Mechanical:

A.使用寿命\Durability:500 cycles



 技术支持 13975145315			版次	比例	4:1	料号	CT3.640.694C
			1.未注公差按ISO2768-1(m) 2.去尽毛刺C0.13max 3.各圆同轴度Ø0.1max			规格	BNC-SMA-KJ-9C
	设计	JAT	2024.01.03	*尺寸为重要尺寸			名称
审核	DF	2024.01.03	单位 mm			 深圳成泰电子有限公司 www.cntitle.net	
批准	DF	2024.01.03					