

公差参数

Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50

材料及电镀

- ①.塑件主体: PA66, UL94V-0
- ②.夹子: 磷青铜, 镀镍
- ③.方盒: 黄铜, 镀镍
- ④.塑件盖板: PA66, UL94V-0
- ⑤.螺丝: M2.0, 钢, 镀锌, 一字槽

电气性能


- 额定电压: 300V
- 额定电流: 8A
- 接触电阻: 20mΩ (Max)
- 绝缘电阻: 500MΩ/DC500V
- 耐电压: AC1600V\1Min
- 使用线径: 28-16AWG 1.5mm²

机械性能

- 温度范围: -40℃ ~ +105℃
- 瞬时温度: +250℃ 5秒
- 扭力: 0.2Nm(1.77lbin)
- 剥线长度: 6-7mm

Ordering Information

XD15EDG		*	*	-	*	-	NP	-	*
Type	默认=开口	PITCH	No. of Pins	Colour					
V=直插	C=插插	2.54*2.54mm	2-24 Pin	Y=Green					
R=带针	A=螺丝	3.5*3.50mm	24 Pin	L=Blue					
K=母座		3.81*3.81mm	2P~29P	O=Orange					
		5.08*5.08mm	3P~39P	R=Red					
		7.62*7.62mm	B=Black					
				GR=Gray					

			GENERAL TOLERANCE	制图 DRAWING	 深圳讯答科技有限公司 Shenzhen Xunda Technology Co., Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	3.81 单排 插拔式 带螺丝 接线端子 母座	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XD15EDGKM-3.81-NP-V	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					

