







REV.	Q'TY	ECN. NO.	APR.	DATE

技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:<20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B
XY-XHB2.54-2A41	2	2.50	5.80
XY-XHB2.54-3A41	3	5.00	8.30
XY-XHB2.54-4A41	4	7.50	10.80
XY-XHB2.54-5A41	5	10.00	13.30
XY-XHB2.54-6A41	6	12.50	15.80
XY-XHB2.54-7A41	7	15.00	18.30
XY-XHB2.54-8A41	8	17.50	20.80
XY-XHB2.54-9A41	9	20.00	23.30
XY-XHB2.54-10A41	10	22.50	25.80
XY-XHB2.54-11A41	11	25.00	28.30
XY-XHB2.54-12A41	12	27.50	30.80
XY-XHB2.54-13A41	13	30.00	33.30
XY-XHB2.54-14A41	14	32.50	35.80
XY-XHB2.54-15A41	15	35.00	38.30
XY-XHB2.54-16A41	16	37.50	40.80
XY-XHB2.54-17A41	17	40.00	43.30



DIMENSION IN mm		TOLERANCE UNLESS OTHERWISE SPECIFIED		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd			
.X±0.35	X.*± 5°	APR.	Alex	TITLE: XHB2.5MM HOUSING			
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-XHB2.54-NA41			
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ.	CUSTOMER DRAWING		
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A				