







REV.	Q'TY	ECN. NO.	APR.	DATE




技术要求 Specification:

1. 材质 Material: PA66 UL94V-0;
2. 额定电流 Current rating: 3.0A AC, DC
3. 额定电压 Voltage rating: 250V AC, DC
4. 温度范围 Temperature range: -25℃ to +85℃
5. 接触电阻 Contact resistance: $\leq 20m\Omega$
6. 绝缘电阻 Insulation resistance: >math>1000M\Omega</math>
7. 耐压 Withstand voltage: 1000V AC/minute
8. 零件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C	D
XY-XH2.54-2A41	2	2.50	5.70	3.70	3.70
XY-XH2.54-3A41	3	5.00	8.20	6.20	6.20
XY-XH2.54-4A41	4	7.50	10.70	8.70	8.70
XY-XH2.54-5A41	5	10.00	13.20	11.20	11.20
XY-XH2.54-6A41	6	12.50	15.70	13.70	13.70
XY-XH2.54-7A41	7	15.00	18.20	16.20	16.20
XY-XH2.54-8A41	8	17.50	20.70	18.70	18.70
XY-XH2.54-9A41	9	20.00	23.20	21.20	21.20
XY-XH2.54-10A41	10	22.50	25.70	23.70	23.70
XY-XH2.54-11A41	11	25.00	28.20	26.20	26.20
XY-XH2.54-12A41	12	27.50	30.70	28.70	28.70
XY-XH2.54-13A41	13	30.00	33.20	31.20	31.20
XY-XH2.54-14A41	14	32.50	35.70	33.70	33.70
XY-XH2.54-15A41	15	35.00	38.20	36.20	36.20
XY-XH2.54-16A41	16	37.50	40.70	38.70	38.70



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.35	X.*± 5°	APR.	Alex	TITLE: XH2.5MM HOUSING
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-XH2.54-NA41
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ.  CUSTOMER DRAWING SIZE A4 SCALE 1:1 SHEET 1/1 REV. A