





REV.	Q'TY	ECN. NO.	APR.	DATE



Part No	Pin	A	B	C
XY-SH1.0-2A41	2	1.00	5.00	2.40
XY-SH1.0-3A41	3	2.00	6.00	3.40
XY-SH1.0-4A41	4	3.00	7.00	4.40
XY-SH1.0-5A41	5	4.00	8.00	5.40
XY-SH1.0-6A41	6	5.00	9.00	6.40
XY-SH1.0-7A41	7	6.00	10.00	7.40
XY-SH1.0-8A41	8	7.00	11.00	8.40
XY-SH1.0-9A41	9	8.00	12.00	9.40
XY-SH1.0-10A41	10	9.00	13.00	10.40
XY-SH1.0-11A41	11	10.00	14.00	11.40
XY-SH1.0-12A41	12	11.00	15.00	12.40
XY-SH1.0-13A41	13	12.00	16.00	13.40
XY-SH1.0-14A41	14	13.00	17.00	14.40
XY-SH1.0-15A41	15	14.00	18.00	15.40
XY-SH1.0-16A41	16	15.00	19.00	16.40
XY-SH1.0-17A41	17	16.00	20.00	17.40
XY-SH1.0-18A41	18	17.00	21.00	18.40
XY-SH1.0-19A41	19	18.00	22.00	19.40
XY-SH1.0-20A41	20	19.00	23.00	20.40

技术要求 Specification:

1、材质 Material: PA66 UL94V-0;

2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR.	Alex	TITLE: SH1.0MM HOUSING	
.XX±0.25	.X.*± 3°	CHK.	Jack	DWG NO. XY-SH1.0-NA41	
.XXX±0.15	.XX.*± 1°	DRA.	Can	PROJ.	CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A