





| | | | | |
|------|------|----------|------|------|
| REV. | Q'TY | ECN. NO. | APR. | DATE |
| | | | | |



| Part No | Pin | A | B | C |
|----------------|-----|-------|-------|-------|
| XY-SH1.0-2A41 | 2 | 1.00 | 5.00 | 2.40 |
| XY-SH1.0-3A41 | 3 | 2.00 | 6.00 | 3.40 |
| XY-SH1.0-4A41 | 4 | 3.00 | 7.00 | 4.40 |
| XY-SH1.0-5A41 | 5 | 4.00 | 8.00 | 5.40 |
| XY-SH1.0-6A41 | 6 | 5.00 | 9.00 | 6.40 |
| XY-SH1.0-7A41 | 7 | 6.00 | 10.00 | 7.40 |
| XY-SH1.0-8A41 | 8 | 7.00 | 11.00 | 8.40 |
| XY-SH1.0-9A41 | 9 | 8.00 | 12.00 | 9.40 |
| XY-SH1.0-10A41 | 10 | 9.00 | 13.00 | 10.40 |
| XY-SH1.0-11A41 | 11 | 10.00 | 14.00 | 11.40 |
| XY-SH1.0-12A41 | 12 | 11.00 | 15.00 | 12.40 |
| XY-SH1.0-13A41 | 13 | 12.00 | 16.00 | 13.40 |
| XY-SH1.0-14A41 | 14 | 13.00 | 17.00 | 14.40 |
| XY-SH1.0-15A41 | 15 | 14.00 | 18.00 | 15.40 |
| XY-SH1.0-16A41 | 16 | 15.00 | 19.00 | 16.40 |
| XY-SH1.0-17A41 | 17 | 16.00 | 20.00 | 17.40 |
| XY-SH1.0-18A41 | 18 | 17.00 | 21.00 | 18.40 |
| XY-SH1.0-19A41 | 19 | 18.00 | 22.00 | 19.40 |
| XY-SH1.0-20A41 | 20 | 19.00 | 23.00 | 20.40 |

技术要求 Specification:

1、材质 Material: PA66 UL94V-0;

2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

| DIMENSION IN mm | | 厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd | | | |
|--------------------------------------|-----------|--|-----------|------------------------|------------------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED | | | | | |
| .X±0.35 | X.*± 5' | APR. | Alex | TITLE: SH1.0MM HOUSING | |
| .XX±0.25 | .X.*± 3' | CHK. | Jack | DWG NO. XY-SH1.0-NA41 | |
| .XXX±0.15 | .XX.*± 1' | DRA. | Can | PROJ. | CUSTOMER DRAWING |
| | | SIZE A4 | SCALE 1:1 | SHEET 1/1 | REV. A |