






REV.	Q'TY	ECN. NO.	APR.	DATE



技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:2.0A AC,DC
3. 额定电压 Voltage rating:100V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:800V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



Part No	Pin	A	B	C
XY-PH2.0-2A41	2	2.00	5.70	4.50
XY-PH2.0-3A41	3	4.00	7.70	6.50
XY-PH2.0-4A41	4	6.00	9.70	8.50
XY-PH2.0-5A41	5	8.00	11.70	10.50
XY-PH2.0-6A41	6	10.00	13.70	12.50
XY-PH2.0-7A41	7	12.00	15.70	14.50
XY-PH2.0-8A41	8	14.00	17.70	16.50
XY-PH2.0-9A41	9	16.00	19.70	18.50
XY-PH2.0-10A41	10	18.00	21.70	20.50
XY-PH2.0-11A41	11	20.00	23.70	22.50
XY-PH2.0-12A41	12	22.00	25.70	24.50
XY-PH2.0-13A41	13	24.00	27.70	26.50
XY-PH2.0-14A41	14	26.00	29.70	28.50
XY-PH2.0-15A41	15	28.00	31.70	30.50
XY-PH2.0-16A41	16	30.00	33.70	32.50

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.35	X.*± 5*	APR. Alex	TITLE: PH2.0MM HOUSING	
.XX±0.25	.X*± 3*	CHK. Jack	DWG NO. XY-PH2.0-NA41	
.XXX±0.15	.XX*± 1*	DRA. Can	PROJ.  CUSTOMER DRAWING	
		SIZE A4	SCALE 1:1	SHEET 1/1
		REV. A		