






REV.	Q'TY	ECN. NO.	APR.	DATE

技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:1.0A AC,DC
3. 额定电压 Voltage rating:50V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥100MΩ
7. 耐压Withstand voltage:250V AC/minute
8. 塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C
XY-MX1.25-2A41	2	1.25	4.30	3.00
XY-MX1.25-3A41	3	2.50	5.55	4.25
XY-MX1.25-4A41	4	3.75	6.80	5.50
XY-MX1.25-5A41	5	5.00	8.05	6.75
XY-MX1.25-6A41	6	6.25	9.30	8.00
XY-MX1.25-7A41	7	7.50	10.55	9.25
XY-MX1.25-8A41	8	8.75	11.80	10.50
XY-MX1.25-9A41	9	10.00	13.05	11.75
XY-MX1.25-10A41	10	11.25	14.30	13.00
XY-MX1.25-11A41	11	12.50	15.55	14.25
XY-MX1.25-12A41	12	13.75	16.80	15.50
XY-MX1.25-13A41	13	15.00	18.05	16.75
XY-MX1.25-14A41	14	16.25	19.30	18.00
XY-MX1.25-15A41	15	17.50	20.55	19.25
XY-MX1.25-16A41	16	18.75	21.80	20.50



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecomm Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: MX1.25MM HOUSING		
.X±0.35	X.*±5°	APR.	Alex	DWG NO. XY-MX1.25-NA41
.XX±0.25	.X.*±3°	CHK.	Jack	PROJ. CUSTOMER DRAWING
.XXX±0.15	.XX.*±1°	DRA.	Can	SIZE A4 SCALE 1:1 SHEET 1/1 REV. A