

REV.	Q'TY	ECN. NO.	APR.	DATE

技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:1.0A AC,DC
3. 额定电压 Voltage rating: 50V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:<30mΩ
6. 绝缘电阻Insulation resistance:>100MΩ
7. 耐压Withstand voltage:500V AC/minute
8. 塑件表面平整光洁, 无明显毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C	D
XY-GH1.25-2A41	2	1.25	2.00	3.75	
XY-GH1.25-3A41	3	2.50	3.20	5.00	
XY-GH1.25-4A41	4	3.75	4.30	6.25	
XY-GH1.25-5A41	5	5.00	4.30	7.50	6.25
XY-GH1.25-6A41	6	6.25	6.25	8.75	8.75
XY-GH1.25-7A41	7	7.50	6.25	10.00	8.75
XY-GH1.25-8A41	8	8.75	6.25	11.25	8.75
XY-GH1.25-9A41	9	10.00	6.25	12.50	8.75
XY-GH1.25-10A41	10	11.25	8.30	13.75	10.70
XY-GH1.25-11A41	11	12.50	8.30	15.00	10.70
XY-GH1.25-12A41	12	13.75	8.30	16.25	10.70
XY-GH1.25-13A41	13	15.00	8.30	17.50	10.70
XY-GH1.25-14A41	14	16.25	8.30	18.75	10.70
XY-GH1.25-15A41	15	17.50	8.30	20.00	10.70
XY-GH1.25-16A41	16	18.75	8.30	21.25	

DIMENSION IN mm		APR. Alex		TITLE: GH1.25MM HOUSING	
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	CHK. Jack	DWG NO. XY-GH1.25-NA41		
.XX±0.25	.X*± 3°		PROJ. CUSTOMER DRAWING		
.XXX±0.15	.XX*± 1°	DRA. Can	SIZE A4	SCALE 1:1	SHEET 1/1
			REV. A		

