



Specifications:

规格:

Voltage rating:100V AC/DC

额定电压: 100V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:800V AC/minute

耐受电压: 800V AC/分钟

Temperature range:-40℃~+85℃

温度范围: -40℃~+85℃

Insulation resistance:500MΩ min

绝缘电阻: 500MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2011 H M - XX A - N0

① ② ③ ④ ⑤ ⑥

1. Series No

2. Category:H-HSG

3. Category:M-Male Housing

4. Row No.Pin No:XX-02~15 Pin

5. Special No:A-With Lock

6. Material:N0-PA66 UL94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	4.70	10	18.00	20.70
03	4.00	6.70	11	20.00	22.70
04	6.00	8.70	12	22.00	24.70
05	8.00	10.70	13	24.00	26.70
06	10.00	12.70	14	26.00	28.70
07	12.00	14.70	15	28.00	30.70
08	14.00	16.70	16	30.00	32.70
09	16.00	18.70		/	/

X2011HM-XXA-N0	PA66	X2011W	X2011TF
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

广东星坤科技股份有限公司

Δ 姓	日期
Δ 姓	日期
Δ 姓	日期

文件工程草

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
					UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.0mm Crimp Style Connector
CHKD	UNIT: mm/in	PART NO.: X2011HM-XXA-N0
APPD	SIZE: A4	DWG NO.: X-X2011HM-XXA-N0
		WEIGHT
		SHEET
		REVISION