



Pin	A	B	C
2	1.25	7.50	
3	2.50	8.75	
4	3.75	10.00	2.50
5	5.00	11.25	3.75
6	6.25	12.50	5.00
7	7.50	13.75	6.25
8	8.75	15.00	7.50
9	10.00	16.25	8.75
10	11.25	17.50	10.00
11	12.50	18.75	11.25
12	13.75	20.00	12.50
13	15.00	21.25	13.75
14	16.25	22.50	15.00
15	17.50	23.75	16.25
16	18.75	25.00	17.50



技术参数
 间距: 1.25
 温度范围: -25~+85°C
 额定电压: 125V AC, DC
 额定电流: 1.0A AC, DC
 接触电阻: 20mΩ
 绝缘电阻: 100MΩ
 耐压: 500V AC/minute

线性公差 / General Tolerance		材料 / Material	
X	±0.2	①塑座: LCP 本色 ②接触针: 黄铜(镀锡) ③焊片: 黄铜(镀锡)	
X.X	±0.1		
X.XX	±0.05		
角度公差 / Angle Tolerance		阶段标记	
X°	±5.0°	版本	比例
X.X°	±3.0°	2.0	1:1
X.XX°	±1.0°	共 1 张 第 1 张	
视角 / Projection		品名 / ProduceName	
		MX1.25 卧贴	
		型号 / Model	
		ZX-MX1.25-n*PWT	
标记	变更内容	签名	年月日
绘图			
审核			
工艺		批准	



品名 / ProduceName

MX1.25 卧贴

型号 / Model

ZX-MX1.25-n*PWT