



3P~15P Shape

2P Shape

Specifications_{XKB}

规格:

Voltage rating:500V AC/DC

额定电压: 500V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥500MΩ

绝缘电阻: ≥500MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ _{XKB}

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

X8821 HM-XX L- N0

- ①
- ②
- ③
- ④
- ⑤

① Series No.

② Category:HM-HSG

③ Row No.Pin No.: XX-Single Row;

④ Plug the Pin&Special No:L-With Lock

⑤ Material:NO-PA66 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.50	7.50	5.70	09	20.00	25.00	23.20
03	5.00	10.00	8.20	10	22.50	27.50	25.70
04	7.50	12.50	10.70	11	25.00	30.00	28.20
05	10.00	15.00	13.20	12	27.50	32.50	30.70
06	12.50	17.50	15.70	13	30.00	35.00	33.20
07	15.00	20.00	18.20	14	32.50	37.50	35.70
08	17.50	22.50	20.70	15	35.00	40.00	38.20

X8821HM-XXL-N0	Nylon 66 UL 94V-0	X8821TF-L	X8821W-L
PART NO	Material	Suitable SWB terminal	Mates With XKB Wafer

由 Autodes 教育版产品制作

ΔX					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4
	REVISIONS				L > 63	±0.5
UNSPECIFIED TOLERANCES						
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

DSND		SCALE: N/A	MODEL TYPE: 2.54 mm Crimp Style Connector
DWN		VIEW:	PART NO.: X8821HM-XXL-N0
CHKD		UNIT: mm/in	DWG NO.:
APPD		SIZE: A4	

MKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISIC
	1/1	A0