



2~4A

PCB LAYOUT

SPECIFICATIONS

- 1、 Current Rating: 3A AC, DC
- 2、 Voltage Rating: 250V AC, DC
- 3、 Temperatuer Range: -25℃~+85℃
- 4、 Contact Resistance: 20mΩ Max
- 5、 Insulation Resistance: 1000MΩ Min
- 6、 Withstanding Voltang: 1000V AC/minute
- 7、 Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2504-02A	2.50	7.50
A2504-03A	5.00	10.00
A2504-04A	7.50	12.50
A2504-05A	10.00	15.00
A2504-06A	12.50	17.50
A2504-07A	15.00	20.00
A2504-08A	17.50	22.50
A2504-09A	20.00	25.00
A2504-10A	22.50	27.50
A2504-11A	25.00	30.00
A2504-12A	27.50	32.50
A2504-20A	47.50	52.50

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.	版本 REV.	A
			X±0.25	X°±2°				
.X±0.20	.X°±1°							
			.XX±0.15	.XX°±0.5°	核准 APPROVAL	兆星精密电子 (深圳) 有限公司		
			.XXX±0.10	.XXX°±0.5°			单位 UNITS	MM

料号 PART NO. ZX-HA2.54-nPZZ
 品名 TITLE HA2.54 直针 n * P
 客户料号 CUTM. NO.
 版本 REV. A
 页次 SHEET 1/1
 兆星精密电子 (深圳) 有限公司