








RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV. ECN. NO. APPD.



CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Operating Life	≥30000次
Contact rating	50mA@12V DC.
Insulation resistance	100MΩ min.
Contact resistance	100MΩ max
Dielectric Strength	250 V AC(1mm)
Travel	0.25±0.1MM

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR
E	button	PPA	1	black
D	Cover plate	Iron	1	copper-tin
C	shrapnel	Phosphor copper	1	Compound silver
B	ontology	PPA	1	black
A	card	brass	1	Silver plating

Type	Operating Force (gf)	Height mm	Button	Leads Shape (G, J, T)	Ground pin (0, 1)	Pegs Option (0, 1)	
YTS1S016	2	260±50	A	4.3	B(Black)	T	0
			B	4.5			
			C	5.0			
			D	5.5			
			E	6.0			
			F	6.5			
			G	7.0			
			H	7.5			
			I	8.0			
			J	8.5			
			K	9.0			
L	9.5						
YTS1S016	1	160±50	A	4.3	B(Black)	T	0
			B	4.5			
			C	5.0			
			D	5.5			
			E	6.0			
			F	6.5			
			G	7.0			
			H	7.5			
			I	8.0			
			J	8.5			
			K	9.0			
L	9.5						

THESE DRAWINGS SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANYMANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD
Email at info@yiyuanswitches.com

X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	
.XX ±0.10	.XX° ± 0.5°	
.XXX ± 0.05		

MAT'L	FINISH	Q'TY
-------	--------	------

yiYUAN 深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO. YTS1S016	TITLE: TACTILE SWITCH 6x6两脚
APPD: ROGER	DWG NO.: YTS1S016
CHKD: ROC	SCALE SHEET REV. 1/1 1/1 A1
DR: BILLY WANG 2020/08/21	