



| Part No | Pin | A | B | C |
|--------------------|-----|-------|-------|-------|
| WAFER-HA2.54-2PLB | 2 | 2.50 | 10.00 | 7.50 |
| WAFER-HA2.54-3PLB | 3 | 5.00 | 12.50 | 10.00 |
| WAFER-HA2.54-4PLB | 4 | 7.50 | 15.00 | 12.50 |
| WAFER-HA2.54-5PLB | 5 | 10.00 | 17.50 | 15.00 |
| WAFER-HA2.54-6PLB | 6 | 12.50 | 20.00 | 17.50 |
| WAFER-HA2.54-7PLB | 7 | 15.00 | 22.50 | 20.00 |
| WAFER-HA2.54-8PLB | 8 | 17.50 | 25.00 | 22.50 |
| WAFER-HA2.54-9PLB | 9 | 20.00 | 27.50 | 25.00 |
| WAFER-HA2.54-10PLB | 10 | 22.50 | 30.00 | 27.50 |
| WAFER-HA2.54-11PLB | 11 | 25.00 | 32.50 | 30.00 |
| WAFER-HA2.54-12PLB | 12 | 27.50 | 35.00 | 32.50 |
| WAFER-HA2.54-13PLB | 13 | 30.00 | 37.50 | 35.00 |
| WAFER-HA2.54-14PLB | 14 | 32.50 | 40.00 | 37.50 |
| WAFER-HA2.54-15PLB | 15 | 35.00 | 42.50 | 40.00 |
| WAFER-HA2.54-16PLB | 16 | 37.50 | 45.00 | 42.50 |

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 1000V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

| | | | | |
|---------------------------------------|-----------|----------|---|-------------------|
| MANUFACTURE DWG | | | 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd | |
| UNLESS OTHERWISE SPECIFIED TOLERANCES | | | TITLE: WAFER XHB2.54 立贴带扣 | |
| DECIMALS: | ANGLES: | | PAR | WAFER-HA2.54-NPLB |
| X.:±0.2 | X'.:±5° | | DWN | |
| .X:±0.1 | X.X':±3° | | CHKD | |
| .XX:±0.05 | X.XX':±1° | | APVD | |
| CUSTOMER COPY | | SCALE1:1 | UNIT:MM | |
| | | SIZE:A4 | SHEET:1F1 | REV:A |