




技术要求 Specification:

- 1、材质 Material: PA66 UL94V-0:
- 2、额定电流 Current rating: 2.0A AC, DC
- 3、额定电压 Voltage rating: 100V AC, DC
- 4、温度范围 Temperature range: -25°C to $+85^{\circ}\text{C}$
- 5、接触电阻 Contact resistance: $\leq 20\text{m}\Omega$
- 6、绝缘电阻 Insulation resistance: $\geq 1000\text{M}\Omega$
- 7、耐压 Withstand voltage: 800V AC/minute
- 8、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



Part No	Pin	A	B	C
WAFER-PH2.0-2PJK	2	2.00	5.70	4.50
WAFER-PH2.0-3PJK	3	4.00	7.70	6.50
WAFER-PH2.0-4PJK	4	6.00	9.70	8.50
WAFER-PH2.0-5PJK	5	8.00	11.70	10.50
WAFER-PH2.0-6PJK	6	10.00	13.70	12.50
WAFER-PH2.0-7PJK	7	12.00	15.70	14.50
WAFER-PH2.0-8PJK	8	14.00	17.70	16.50
WAFER-PH2.0-9PJK	9	16.00	19.70	18.50
WAFER-PH2.0-10PJK	10	18.00	21.70	20.50
WAFER-PH2.0-11PJK	11	20.00	23.70	22.50
WAFER-PH2.0-12PJK	12	22.00	25.70	24.50
WAFER-PH2.0-13PJK	13	24.00	27.70	26.50
WAFER-PH2.0-14PJK	14	26.00	29.70	28.50
WAFER-PH2.0-15PJK	15	28.00	31.70	30.50
WAFER-PH2.0-16PJK	16	30.00	33.70	32.50

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: PH2.0MM HOUSING
			PAR WAFER-PH2.0-NPJK
DECIMALS:	ANGLES:		DWN
.X±0.30	X:±1°		CHKD
.XX±0.20		APVD	SCALE 1:1 UNIT:MM
.XXX±0.10		CUSTOMER COPY	SIZE:A4 SHEET:1F1
			REV:A

