



Part No	Pin	A	B	C
WAFER-XH2.54-2PLB	2	2.50	10.00	7.50
WAFER-XH2.54-3PLB	3	5.00	12.50	10.00
WAFER-XH2.54-4PLB	4	7.50	15.00	12.50
WAFER-XH2.54-5PLB	5	10.00	17.50	15.00
WAFER-XH2.54-6PLB	6	12.50	20.00	17.50
WAFER-XH2.54-7PLB	7	15.00	22.50	20.00
WAFER-XH2.54-8PLB	8	17.50	25.00	22.50
WAFER-XH2.54-9PLB	9	20.00	27.50	25.00
WAFER-XH2.54-10PLB	10	22.50	30.00	27.50
WAFER-XH2.54-11PLB	11	25.00	32.50	30.00
WAFER-XH2.54-12PLB	12	27.50	35.00	32.50
WAFER-XH2.54-13PLB	13	30.00	37.50	35.00
WAFER-XH2.54-14PLB	14	32.50	40.00	37.50
WAFER-XH2.54-15PLB	15	35.00	42.50	40.00
WAFER-XH2.54-16PLB	16	37.50	45.00	42.50

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 1000V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

MANUFACTURE DWG			东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WAFER 2.54 立贴	
DECIMALS:	ANGLES:	CUSTOMER COPY	PAR	WAFER-XH2.54-NPLB
X.:±0.2	X'.:±5°		DWN	
.X:±0.1	X.X':±3°		CHKD	
.XX:±0.05	X.XX':±1°		APVD	
		SCALE1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A