




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.03.27	



Current rating: 3A AC/DC
 额定电流: 3A AC/DC
 Temperature range: -40°C ~ +125°C
 温度范围: -40°C ~ +125°C

K 174051 H M - 2xxx - N0
 ① ② ③ ④ ⑤ ⑥

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Welding Board Angle:M-Male Housing
- 5.Row No.Pin No:2xxx-2x06 Pin
- 6.Material:N0-PA66 UL94V-0

K174051HM-2x06-N0	PA66	K174051W	K174051T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

SECTION:A-A

ANGULAR	±5°
X.	±0.40
X.X	±0.30
X.XX	±0.20
X.XXX	±0.15
UNSPECIFIED TOLERANCES	

XKBTEK

DESIGN
CHECKED
APPROVED

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
2.5mm Automobile connector
PART NO.:
K174051HM-2x06-N0
DWG NO.:

XKB INDUSTRIAL PRECISION CO., LIMITED

SCALE PAGE REVISION
N/A 1/1 A0